




# 944 Professional UV/VIS Detector Vario


2.944.0010

The 944 Professional UV/VIS Detector Vario is the intelligent UV/VIS detector from Metrohm. It permits a secure and reliable quantification of substances active in the ultraviolet or visible range. Detection takes place via a Diode Array.

## Phạm vi giao hàng 2.944.0010

| Qt.   | Order no.  | Description                            |
|-------|------------|----------------------------------------|
| 1 PCS | 1.944.0010 | 944 Professional UV/VIS Detector Vario |

The 944 Professional UV/VIS Detector Vario is the intelligent UV/VIS detector from Metrohm. It permits a secure and reliable quantification of substances active in the ultraviolet or visible range. Detection takes place via a Diode Array.



2 PCS

6.1831.100

PEEK capillary 0.25 mm i.d., 1 m



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



1 PCS

6.2744.070

Pressure screw short

Short version. With UNF 10/32 connection. 5 pieces. For the connection of PEEK capillaries



1 PCS

6.2839.130

Flow-through cell for 944

PEEK flow-through cell for 944 Professional UV/VIS Detector Vario



## Phụ kiện tùy chọn

| Order no.  | Description                                                                                                                                                                                                                                                                         |                                                                                       |
|------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 6.2061.100 | Bottle holder for Professional IC instruments<br><br>Instrument cover and bottle holder for Professional IC instruments.                                                                                                                                                            |    |
| 6.2061.110 | Tray with sensor for Professional IC Instruments                                                                                                                                                                                                                                    |    |
| 6.2061.120 | System Connector<br><br>Connects an IC module with the footprint of a Professional IC with a Compact IC                                                                                                                                                                             |  |
| 2.943.0110 | 943 Professional Reactor Vario<br><br>The 943 Professional Reactor Vario is a heatable reactor, especially developed for pre- and post-column derivatization. It captivates by its robustness, the fast heating rate and the possibility of carrying out reactions at up to 150 °C. |  |

2.943.0210

## 943 Professional Thermostat Vario

The 943 Professional Thermostat Vario is a stand-alone column oven for up to two columns with a maximum length of 150 mm. It captivates by its fast heating rate and the possibility of operating two separation columns together at up to 80°C.




---

6.2764.000

## Replacement seals to 62839130

Set of seals for Flow cell 10 mm (6.2839.130) to UV/VIS instruments



---

6.2804.060

## Deuterium lamp (UV) for UV/VIS instruments

Replacement bulb for the UV range



---

6.2804.100

## Halogen lamp (Vis) for Professional UV/VIS Detector

Spare lamp for the visible range for the 944 Professional UV/VIS Detector Vario

