



样品架，12 x 6 mL，(Al)

6.2041.210

与 889 IC Sample Center 适配的样品架，用于 12 个样品容器。可使用以下样品容器：6.2419.000。

材料：铝 (Al)

Optional accessories

6.1448.050
铝隔膜盖 / 1000片

包括铝密封铝箔。



6.2419.000
样品瓶 6 mL, 1000 件

样品瓶，用于最多 6 mL 样品，适用于隔垫 6.1448.050，1000 件



6.2621.110
弯边钳

弯边钳，用于密封6 毫升的样品瓶。与774卡氏炉样品处理系统一起使用。



6.2419.007
样品瓶 6 mL, 100 件

样品瓶, 用于最多 6 mL 样品, 适用于隔垫 6.1448.057, 100 件



6.2420.007
带螺纹的 8 mL 样品瓶, 100 个

带螺纹的 8 mL 样品瓶, 适用于转锁 6.1448.067, 100 个



6.1448.067
带隔垫的转锁, 100 个

带隔垫的转锁, 适用于 8 mL 样品瓶, 6.2420.007, 100 个



6.1448.057
铝隔膜盖 / 100片

包括密封铝箔。

